



## Work platform individual module, Type: C



### Order data

Order number	966150 C
GTIN	4003866402625
Item class	96Z

### Description

#### Version:

Extremely robust, torsion-resistant, corrosion-proof, and weatherproof aluminium alloy structure. Steps of serrated aluminium plate 555×250 mm.

Modular structure allows changes and extensions.

Add-on modules available for 4 different heights.

The two-step basic module with up to 3 add-on steps is suitable for mobile use. Add-on modules available from module type B.

#### Standard:

**DIN EN 14183.**

### Technical description

Module combination	B+C
Rung/step depth	250 mm
Working height	2.4 m
Material	Overall light alloy design; steps of ribbed aluminium plate.
Type of step	Step
Platform depth	0.8 m
Platform height without railing	0.4 m

Weight of module combination	8.7 kg
Standard	DIN EN 14183
Rung/step width	555 mm
Weight of individual module	3.9 kg
Accessibility	single-sided
Number of steps including platform	2
Ladders and platforms load capacity	150 kg
Type of product	Work platform