

**Garant****Through hole machine tap, uncoated, MF: M18X2****Order data**

Order number	130000 M18X2
GTIN	4045197998668
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 2 mm

Overall length L: 125 mm

Shank  $\varnothing D_s$ : 14 mmShank square  $\square$ : 11 mmTapping hole  $\varnothing$ : 16 mm**Technical description**

Shank $\varnothing D_s$	14 mm
Thread $\varnothing$	18 mm
Thread depth	54 mm
Shank square $\square$	11 mm
Overall length L	125 mm
Number of clamping slots	3

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Standard	DIN 376
Tool material	HSS E
Tapping hole Ø	16 mm
Thread pitch	2 mm
Number of cutting edges Z	3
Thread type	M
Thread size	M18×2
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap