

**Garant**
**Jobber drill HSS-E N, uncoated, Ø DC h8: 12,5mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 114400 12,5   |
| GTIN         | 4045197018267 |
| Item class   | 11B           |

**Description**
**Version:**

**Profile ground:** this ensures high concentricity and pitch accuracy. Precision ground point. Drill for production use.

**Reinforced core,** bright finish.

With point geometry shape C from size 2 mm

**Recommendation:**
**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

**Technical description**

|   |              |
|---|--------------|
| Nominal Ø D <sub>c</sub>                          | 12.5 mm      |
| Number of cutting edges Z                         | 2            |
| Feed f in steel < 750 N/mm <sup>2</sup>           | 0.16 mm/rev. |
| Flute length L <sub>c</sub>                       | 101 mm       |
| Tolerance nominal Ø                               | h8           |
| Shank Ø D <sub>s</sub>                            | 12.5 mm      |
| Overall length L                                  | 151 mm       |
| Standard  | DIN 338      |
| recommended maximum drilling depth L <sub>2</sub> | 82.3 mm      |
| Point angle                                       | 130 degrees  |
| Shank   | Plain shank  |

|                 |              |
|-----------------|--------------|
| Coating         | uncoated     |
| Tool material   | HSS E        |
| Type            | N            |
| Through-coolant | no           |
| Colour ring     | red          |
| Type of product | Jobber drill |

### User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm <sup>2</sup>  | suitable                                  | 40 m/min       | P        |
| Steel < 750 N/mm <sup>2</sup>  | suitable                                  | 30 m/min       | P        |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  | 25 m/min       | P        |
| Steel < 1100 N/mm <sup>2</sup> | suitable                                  | 10 m/min       | P        |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  | 8 m/min        | P        |
| TOOLOX 33                      | suitable                                  | 8 m/min        | H        |
| INOX < 900 N/mm <sup>2</sup>   | suitable                                  | 12 m/min       | M        |
| INOX > 900 N/mm <sup>2</sup>   | suitable only under restricted conditions | 8 m/min        | M        |
| Ti > 850 N/mm <sup>2</sup>     | suitable only under restricted conditions | 5 m/min        | S        |
| GG(G)                          | suitable                                  | 25 m/min       | K        |
| CuZn                           | suitable only under restricted conditions | 80 m/min       | N        |
| Uni                            | suitable                                  |                |          |
| Oil                            | suitable                                  |                |          |
| wet maximum                    | suitable                                  |                |          |