



## Jobber drill HSS-E N, uncoated, Ø DC h8: 4,9mm



### Order data

Order number	114405 4,9
GTIN	4045197534941
Item class	12B

### Description

#### Version:

**Profile ground:** this ensures high concentricity and pitch accuracy. Precision ground point. Drill for production use.

With point geometry shape C from size 2 mm

#### Recommendation:

#### Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

### Technical description

Feed f in steel < 750 N/mm <sup>2</sup>	0.05 mm/rev.
Number of cutting edges Z	2
Nominal Ø D <sub>c</sub>	4.9 mm
Flute length L <sub>c</sub>	52 mm
Tolerance nominal Ø	h8
Shank Ø D <sub>s</sub>	4.9 mm
Overall length L	86 mm
Standard	DIN 338
recommended maximum drilling depth L <sub>2</sub>	44.7 mm
Point angle	135 degrees
Shank	Plain shank
Coating	uncoated

Tool material	HSS E
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	35 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	28 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	22 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	8 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	6 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	8 m/min	M
Oil	suitable		
wet maximum	suitable		