

Ansell**Pair of chemical protective gloves AlphaTec® Solvex® 37-675, Glove size: 8****Order data**

Order number	094740 8
GTIN	10076490447288
Item class	04P

Description**Version:**

Category III safety gloves.

AlphaTec® Solvex® 37-675. Re-usable nitrile gloves for safe handling of aggressive chemicals. The roughened finish increases the security of grip. The Sol-Vex® hammered finish gives the glove a smooth surface that decreases indirect costs thanks to fewer rejects of fragile parts. Backing material velourised.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Permeation time for acetone 99 %	<10 min
Permeation time for isopropanol 99 %	>480 min
Permeation time for acetonitrile 99 %	<10 min
Permeation time for cyclohexane 99 %	>480 min
Permeation time for sodium hydroxide 40 %	>480 min

Wall thickness	0.38 mm
Permeation time for methanol 99 %	10-30 min
Permeation time for sulphuric acid 96 %	30-40 min
Glove size	8
Series	AlphaTec®
Type of glove	Chemicals protection gloves
Protection category	Category III
Contents	12
Glove characteristics	Foodstuffs certified
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	free of latex
Protection class	Protection against bacteriological risks to EN 374
EN 374	Type A (JKLOPT)
Resistance to chemicals	JKLOPT
EN 388	4101X
Material	Nitrile
Backing material	Nitrile
AQL	0.65
Application range	All-round
Length	330 mm
Thickness	0.38 mm
Colour	green
Application	reusable
Weight	35.5 g
Cut protection class	FG
Coating	Nitril
Type of product	Chemicals protection gloves

