



Pair of chemical protective gloves Camatril® 730, Glove size: 8



Order data

Order number	094748 8
GTIN	4008198773085
Item class	04Q

Description

Version:

Category III safety gloves.

Camatril® 730. Nitrile gloves with velour cotton and a wide spectrum of chemical resistance characteristics. Good temperature resistance with at the same time good touch sensitivity. Absolutely free of silicones, no effect on paints. Approved for contact with foodstuffs.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Permeation time for cyclohexane 99 %	>480 min
Glove size	8
Permeation time for dimethyl sulphoxide 99 %	60-120 min
Permeation time for sulphuric acid 50 %	>480 min
Permeation time for acetonitrile 99 %	<10 min
Manufacturer's designation	Camatril 730

Permeation time for acetone 99 %	<10 min
Wall thickness	0.4 mm
Permeation time for sulphuric acid 96 %	60-120 min
Permeation time for ethanol 95 %	60-120 min
Permeation time for isopropanol 99 %	240-480 min
Permeation time for methanol 99 %	10-30 min
silicone-free	yes
Permeation time for sodium hydroxide 40 %	240-480 min
Permeation time for sodium hydroxide 50 %	240-480 min
Series	Camatril®
Protection category	Category III
Type of glove	Chemicals protection gloves
Contents	10
Glove characteristics	Foodstuffs certified
Glove characteristics	Silicone-free
Glove characteristics	DMF-free
Glove characteristics	free of latex
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
EN 374	Type A (AJKLOT)
Resistance to chemicals	AJKLOT
EN 388	3001X
Material	Nitrile
Backing material	Nitrile
AQL	0.65
Application range	All-round
Length	310 mm
Thickness	0.4 mm
Colour	green
Application	reusable

Standard/regulation	EN 374
Type of product	Chemicals protection gloves