

Ansell**Pair of chemical protective gloves AlphaTec® Solvex® 37-675, Glove size: 9****Order data**

| | |
|--------------|----------------|
| Order number | 094740 9 |
| GTIN | 10076490447295 |
| Item class | 04P |

Description**Version:**

Category III safety gloves.

AlphaTec® Solvex® 37-675. Re-usable nitrile gloves for safe handling of aggressive chemicals. The roughened finish increases the security of grip. The Sol-Vex® hammered finish gives the glove a smooth surface that decreases indirect costs thanks to fewer rejects of fragile parts. Backing material velourised.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|---|----------|
| Permeation time for isopropanol 99 % | >480 min |
| Permeation time for acetonitrile 99 % | <10 min |
| Glove size | 9 |
| Permeation time for sodium hydroxide 40 % | >480 min |
| Permeation time for acetone 99 % | <10 min |

| | |
|---|---|
| Permeation time for methanol 99 % | 10-30 min |
| Permeation time for sulphuric acid 96 % | 30-40 min |
| Wall thickness | 0.38 mm |
| Permeation time for cyclohexane 99 % | >480 min |
| Series | AlphaTec® |
| Type of glove | Chemicals protection gloves |
| Protection category | Category III |
| Contents | 12 |
| Glove characteristics | Foodstuffs certified |
| Glove characteristics | Suitable for allergy sufferers |
| Glove characteristics | free of latex |
| Protection class | Protection against bacteriological risks to EN 374 |
| EN 374 | Type A (JKLOPT) |
| Resistance to chemicals | JKLOPT |
| EN 388 | 4101X |
| Material | Nitrile |
| Backing material | Nitrile |
| AQL | 0.65 |
| Application range | All-round |
| Length | 330 mm |
| Thickness | 0.38 mm |
| Colour | green |
| Application | reusable |
| Weight | 35.5 g |
| Cut protection class | FG |
| Coating | Nitril |
| Type of product | Chemicals protection gloves |

