

**Pair of chemical protective gloves Camatril® 730, Glove size: 10****Order data**

Order number	094748 10
GTIN	4008198773009
Item class	04Q

Description**Version:**

Category III safety gloves.

Camatril® 730. Nitrile gloves with velour cotton and a wide spectrum of chemical resistance characteristics. Good temperature resistance with at the same time good touch sensitivity. Absolutely free of silicones, no effect on paints. Approved for contact with foodstuffs.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Permeation time for sodium hydroxide 40 %	240-480 min
Permeation time for dimethyl sulphoxide 99 %	60-120 min
Permeation time for acetone 99 %	<10 min
silicone-free	yes
Permeation time for methanol 99 %	10-30 min
Permeation time for sodium hydroxide 50 %	240-480 min

Permeation time for ethanol 95 %	60-120 min
Permeation time for isopropanol 99 %	240-480 min
Permeation time for cyclohexane 99 %	>480 min
Permeation time for acetonitrile 99 %	<10 min
Permeation time for sulphuric acid 96 %	60-120 min
Manufacturer's designation	Camatril 730
Glove size	10
Wall thickness	0.4 mm
Permeation time for sulphuric acid 50 %	>480 min
Series	Camatril®
Type of glove	Chemicals protection gloves
Protection category	Category III
Contents	10
Glove characteristics	Foodstuffs certified
Glove characteristics	Silicone-free
Glove characteristics	DMF-free
Glove characteristics	free of latex
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
EN 374	Type A (AJKLOT)
Resistance to chemicals	AJKLOT
EN 388	3001X
Material	Nitrile
Backing material	Nitrile
AQL	0.65
Application range	All-round
Length	310 mm
Thickness	0.4 mm
Colour	green
Application	reusable

Standard/regulation	EN 374
Type of product	Chemicals protection gloves