



Pair of chemical protective gloves UltraNeo 382, Glove size: 8



Order data

Order number	094772 8
GTIN	3245423824285
Item class	06D

Description

Version:

Category III safety gloves.

UltraNeo 382. Knitted cotton gloves with neoprene coating. Very high wearing comfort and good thermal insulation with outstanding resistance to chemicals. Non-slip profile for increased security of grip.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. EN 374:2016: Type A (ALMNST)

Technical description

Permeation time for isopropanol 99 %	>480 min
Glove size	8
Permeation time for cyclohexane 99 %	30-40 min
Permeation time for dimethyl sulphoxide 99 %	240-480 min
Permeation time for sulphuric acid 50 %	>480 min

Permeation time for sodium hydroxide 50 %	>480 min
Permeation time for acetonitrile 99 %	30-40 min
Wall thickness	0.9 mm
silicone-free	yes
Permeation time for methanol 99 %	120-240 min
Permeation time for sulphuric acid 96 %	60-120 min
Permeation time for sodium hydroxide 40 %	>480 min
Permeation time for ethanol 95 %	240-480 min
Permeation time for acetone 99 %	<10 min
Lining material	knitted cotton
Protection category	Category III
Type of glove	Chemicals protection gloves
Contents	72
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
EN 374:2016	Type A (ALMNST)
Resistance to chemicals	ALMNST
EN 388:2016	2121X
EN 407	X1XXXX
Material	Neoprene
Backing material	Cotton
AQL	1.5
Length	360 mm
Thickness	0.9 mm
Colour	blue
Application	reusable
Coating	Neoprene
Coating variant	Full coating
Type of product	Chemicals protection gloves

