

Garant**Through hole machine tap, uncoated, MF: M19X2****Order data**

Order number	130000 M19X2
GTIN	4045197998750
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 2 mm

Overall length L: 140 mm

Shank \varnothing D_s: 16 mmShank square \square : 12 mmTapping hole \varnothing : 17 mm**Technical description**

Standard	DIN 376
Tapping hole \varnothing	17 mm
Thread \varnothing	19 mm
Thread pitch	2 mm
Number of clamping slots	3
Thread depth	57 mm

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Number of cutting edges Z	3
Shank square □	12 mm
Overall length L	140 mm
Tool material	HSS E
Shank $\varnothing D_s$	16 mm
Thread type	M
Thread size	M19x2
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3xD for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap