



HSS jobber drill Precision roll forged N, uncoated, Ø DC h8: 10mm



Order data

Order number	114020 10
GTIN	4045197010438
Item class	12B

Description

Version:

Roll forged, standard helix angle, core thickness and core taper.

Dimensions to DIN 338.

Robust jobber drill with strengthened core and small chisel point for easy spot drilling and accurate centring of the designated hole. **Precision roll forged flutes.**

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Note:

Size 14-20: Shank Ø 13 mm with 3 drive flats.

Technical description

Flute length L_c	87 mm
Nominal Ø D_c	10 mm
Feed f in steel < 750 N/mm ²	0.1 mm/rev.
Number of cutting edges Z	2
Tolerance nominal Ø	h8
Shank Ø D_s	10 mm
Overall length L	133 mm
recommended maximum drilling depth L_2	72 mm
Point angle	118 degrees
Shank	Plain shank

Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	45 m/min	N
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
GG(G)	suitable only under restricted conditions	25 m/min	K
Oil	suitable		
wet maximum	suitable		