

Garant
HSS-Co8 jobber drill, TiAlN, Ø DC h8: 2,1mm

Order data

Order number	114550 2,1
GTIN	4045197020703
Item class	11B

Description
Version:

Extremely high heat resistance, very robust due to **strong core**.

With point geometry shape C.

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Technical description

Feed f in stainless steel > 900 N/mm ²	0.02 mm/rev.
Flute length L _c	24 mm
Nominal Ø D _c	2.1 mm
Number of cutting edges Z	2
Tolerance nominal Ø	h8
Shank Ø D _s	2.1 mm
Overall length L	49 mm
Standard	DIN 338
recommended maximum drilling depth L ₂	20.9 mm
Point angle	135 degrees
Shank	Plain shank
Coating	TiAlN

Tool material	HSS Co 8
Helix angle	35 degrees
Through-coolant	no
Colour ring	blue
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 750 N/mm ²	suitable only under restricted conditions	37 m/min	P
Steel < 900 N/mm ²	suitable	31 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	10 m/min	P
INOX < 900 N/mm ²	suitable	20 m/min	M
INOX > 900 N/mm ²	suitable	15 m/min	M
Ti > 850 N/mm ²	suitable	6 m/min	S
Oil	suitable		
wet maximum	suitable		