

**Garant****Through hole machine tap, uncoated, MF: M39X3****Order data**

Order number	130000 M39X3
GTIN	4045197625144
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 3 mm

Overall length L: 200 mm

Shank  $\varnothing$  D<sub>s</sub>: 32 mmShank square  $\square$ : 24 mmTapping hole  $\varnothing$ : 36 mm**Technical description**

Tool material	HSS E
Tapping hole $\varnothing$	36 mm
Number of clamping slots	4
Standard	DIN 376
Shank square $\square$	24 mm
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Thread depth	117 mm
Shank $\varnothing D_s$	32 mm
Thread pitch	3 mm
Thread $\varnothing$	39 mm
Overall length L	200 mm
Number of cutting edges Z	4
Thread type	M
Thread size	M39×3
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap