

Garant
Left-hand thread through hole machine tap, uncoated, MF: M17X2

Order data

Order number	130001 M17X2
GTIN	4062406001360
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS E
 Standard: DIN 376
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 2 mm
 Overall length L: 125 mm
 Shank \varnothing D_s: 14 mm
 Shank square □: 11 mm
 Tapping hole \varnothing : 15 mm

Technical description

Tapping hole \varnothing	15 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05

Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Overall length L	125 mm
Tool material	HSS E
Number of cutting edges Z	3
Thread depth	51 mm
Thread pitch	2 mm
Shank $\varnothing D_s$	14 mm
Standard	DIN 376
Thread \varnothing	17 mm
Shank square \square	11 mm
Number of clamping slots	3
Thread type	MF-LH
Thread size	M17x2
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3xD for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap