

**Garant**
**HSS jobber drill N, uncoated, Ø DC h8 (mm or inch): 1/64**

**Order data**

Order number	114150 1/64
GTIN	4045197364203
Item class	11B

**Description**
**Version:**

Profile ground: Jobber drill with high pitch accuracy and concentricity as well as precision ground point.

Steam tempered from Ø 2.4 mm.

With point geometry shape C from size 4 mm

**Recommendation:**
**Maximum drilling depth:**

$L_2 = L_c - 1.5 \times D_c$ .

**Note:**

Size 16 - 20: Drills with shank Ø 16 mm.

**Technical description**

Number of cutting edges Z	2
Feed f in steel < 750 N/mm <sup>2</sup>	0.03 mm/rev.
Flute length L <sub>c</sub>	5 mm
Inch nominal Ø corresponds to	0.4 mm
Tolerance nominal Ø	h8
Shank Ø D <sub>s</sub>	0.4 mm
Overall length L	20 mm
Standard	DIN 338
recommended maximum drilling depth L <sub>2</sub>	4.4 mm
Point angle	118 degrees

Shank	Plain shank
Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	80 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	45 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	10 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	8 m/min	P
GG(G)	suitable	25 m/min	K
CuZn	suitable	80 m/min	N
Oil	suitable		
wet maximum	suitable		