

**Garant**
**Left-hand thread through hole machine tap, uncoated, MF: M22X1,5**

**Order data**

Order number	130001 M22X1,5
GTIN	4062406001742
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 1.5 mm

Overall length L: 140 mm

Shank  $\varnothing$  D<sub>s</sub>: 18 mm

Shank square □: 14.5 mm

Tapping hole  $\varnothing$ : 20.5 mm

**Technical description**

Number of cutting edges Z	3
Overall length L	140 mm
Number of clamping slots	3
Tool material	HSS E
Shank square □	14.5 mm
Thread depth	66 mm

Standard	DIN 376
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Shank $\varnothing D_s$	18 mm
Tapping hole $\varnothing$	20.5 mm
Thread $\varnothing$	22 mm
Thread pitch	1.5 mm
Thread type	MF-LH
Thread size	M22×1.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring

without

Type of product

Tap