

**Garant**
**Left-hand thread through hole machine tap, uncoated, MF: M3,5X0,5**

**Order data**

Order number	130001 M3,5X0,5
GTIN	4062406000509
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 3 pcs.  
 Special / custom-made product - return not possible  
 Thread type: MF-LH  
 Tool material: HSS E  
 Standard: DIN 371  
 Tolerance class: ISO 1 4H  
 Tolerance class: ISO 1X 4HX  
 Tolerance class: ISO 2 6H  
 Thread pitch: 0.5 mm  
 Overall length L: 56 mm  
 Shank  $\varnothing D_s$ : 4 mm  
 Shank square  $\square$ : 3 mm  
 Tapping hole  $\varnothing$ : 3 mm

**Technical description**

Overall length L	56 mm
Shank $\varnothing D_s$	4 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX

Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Thread Ø	3.5 mm
Number of clamping slots	3
Tapping hole Ø	3 mm
Thread pitch	0.5 mm
Shank square □	3 mm
Number of cutting edges Z	3
Tool material	HSS E
Thread depth	10.5 mm
Standard	DIN 371
Thread type	MF-LH
Thread size	M3.5×0.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap