

**Garant****Left-hand thread through hole machine tap, uncoated, MF: M43X0,5****Order data**

Order number	130001 M43X0,5
GTIN	4062406003302
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 220 mm

Shank  $\varnothing D_s$ : 36 mmShank square  $\square$ : 29 mmTapping hole  $\varnothing$ : 42.5 mm**Technical description**

Thread pitch	0.5 mm
Thread depth	129 mm
Shank square $\square$	29 mm
Shank $\varnothing D_s$	36 mm
Thread $\varnothing$	43 mm
Overall length L	220 mm

Tool material	HSS E
Standard	DIN 376
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Tapping hole Ø	42.5 mm
Number of cutting edges Z	4
Number of clamping slots	4
Thread type	MF-LH
Thread size	M43×0.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap