

Garant
Left-hand thread through hole machine tap, uncoated, MF: M2X0,4

Order data

Order number	130001 M2X0,4
GTIN	4062406000387
Item class	10N

Description
Note:

Delivery time: 91 calendar days
 Minimum order quantity: 25 pcs.
 Special / custom-made product - return not possible
 Thread type: M-LH
 Tool material: HSS E
 Standard: DIN 371
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 0.4 mm
 Overall length L: 45 mm
 Shank $\varnothing D_s$: 2.8 mm
 Shank square \square : 2.1 mm
 Tapping hole \varnothing : 1.6 mm

Technical description

Shank square \square	2.1 mm
Tool material	HSS E
Thread pitch	0.4 mm
Number of clamping slots	3
Shank $\varnothing D_s$	2.8 mm
Tapping hole \varnothing	1.6 mm

Standard	DIN 371
Thread Ø	2 mm
Thread depth	6 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Number of cutting edges Z	3
Overall length L	45 mm
Thread type	M-LH
Thread size	M2×0.4
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap