

**Garant**
**Through hole machine tap, uncoated, MF: M5X0,75**

**Order data**

Order number	130000 M5X0,75
GTIN	4045197997821
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

**Technical description**

Standard	DIN 371
Tool material	HSS E
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX

Tolerance class	6H +0.10
Tolerance class	6H +0.20
Shank square □	4.9 mm
Tapping hole Ø	4.25 mm
Overall length L	70 mm
Thread Ø	5 mm
Thread depth	15 mm
Thread pitch	0.75 mm
Number of cutting edges Z	3
Shank Ø D <sub>s</sub>	6 mm
Number of clamping slots	3
Thread type	M
Thread size	M5×0.75
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap