

Garant
Through hole machine tap, uncoated, MF: M17X1,25

Order data

Order number	130000 M17X1,25
GTIN	4045197998552
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Technical description

Shank square <input type="checkbox"/>	11 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10

Tolerance class	6H +0.20
Number of cutting edges Z	3
Number of clamping slots	3
Shank $\varnothing D_s$	14 mm
Thread \varnothing	17 mm
Overall length L	125 mm
Tapping hole \varnothing	15.75 mm
Thread depth	51 mm
Tool material	HSS E
Standard	DIN 376
Thread pitch	1.25 mm
Thread type	M
Thread size	M17x1.25
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3xD for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap