

**Garant**
**Through hole machine tap, TiN, MF: M15X0,75**

**Order data**

Order number	130005 M15X0,75
GTIN	4062406004736
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

**Technical description**

Tool material	HSS E
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10

Tolerance class	6H +0.20
Tapping hole Ø	14.25 mm
Overall length L	110 mm
Number of clamping slots	3
Shank square □	9 mm
Number of cutting edges Z	3
Thread pitch	0.75 mm
Thread depth	45 mm
Standard	DIN 376
Thread Ø	15 mm
Shank Ø D <sub>s</sub>	12 mm
Thread type	M
Thread size	M15×0.75
Coating	TiN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap