

Garant
Through hole machine tap, uncoated, MF: M45X0,35

Order data

| | |
|--------------|-----------------|
| Order number | 130000 M45X0,35 |
| GTIN | 4045197625397 |
| Item class | 10N |

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Technical description

| | |
|---------------------------------------|------------|
| Thread pitch | 0.35 mm |
| Shank square <input type="checkbox"/> | 29 mm |
| Shank $\varnothing D_s$ | 36 mm |
| Tapping hole \varnothing | 44.65 mm |
| Thread depth | 135 mm |
| Number of cutting edges Z | 4 |
| Tool material | HSS E |
| Tolerance class | ISO 1 4H |
| Tolerance class | ISO 1X 4HX |
| Tolerance class | ISO 2 6H |
| Tolerance class | ISO 2X 6HX |
| Tolerance class | 6H +0.05 |
| Tolerance class | ISO 3 6G |

| | |
|----------------------------------|--|
| Tolerance class | ISO 3X 6GX |
| Tolerance class | 7H |
| Tolerance class | 7HX |
| Tolerance class | 7G |
| Tolerance class | 7GX |
| Tolerance class | 6H +0.10 |
| Tolerance class | 6H +0.20 |
| Number of clamping slots | 4 |
| Standard | DIN 376 |
| Thread Ø | 45 mm |
| Overall length L | 220 mm |
| Thread type | M |
| Thread size | M45×0.35 |
| Coating | uncoated |
| Flank angle | 60 degrees |
| Thread standard | DIN 13 |
| Taper lead form | B |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for through holes |
| Cutting direction | right-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |