

**Garant**
**Through hole machine tap, uncoated, MF: M40X3**

**Order data**

Order number	130000 M40X3
GTIN	4045197625229
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 3 mm

Overall length L: 200 mm

Shank  $\varnothing$  D<sub>s</sub>: 32 mm

Shank square  $\square$ : 24 mm

Tapping hole  $\varnothing$ : 37 mm

**Technical description**

Standard	DIN 376
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05

Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Number of clamping slots	4
Thread pitch	3 mm
Overall length L	200 mm
Thread Ø	40 mm
Number of cutting edges Z	4
Tapping hole Ø	37 mm
Thread depth	120 mm
Shank Ø D <sub>s</sub>	32 mm
Shank square □	24 mm
Tool material	HSS E
Thread type	M
Thread size	M40×3
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap