

Garant**Left-hand thread through hole machine tap, uncoated, MF: M14X1****Order data**

| | |
|--------------|---------------|
| Order number | 130001 M14X1 |
| GTIN | 4062406001094 |
| Item class | 10N |

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: MF-LH
Tool material: HSS E
Standard: DIN 376
Tolerance class: ISO 1 4H
Tolerance class: ISO 1X 4HX
Tolerance class: ISO 2 6H
Thread pitch: 1 mm
Overall length L: 110 mm
Shank $\varnothing D_s$: 11 mm
Shank square \square : 9 mm
Tapping hole \varnothing : 13 mm

Technical description

| | |
|--------------------------|---------|
| Standard | DIN 376 |
| Number of clamping slots | 3 |
| Thread \varnothing | 14 mm |
| Shank square \square | 9 mm |
| Thread depth | 42 mm |
| Shank $\varnothing D_s$ | 11 mm |

| | |
|----------------------------------|--|
| Thread pitch | 1 mm |
| Overall length L | 110 mm |
| Tapping hole Ø | 13 mm |
| Tolerance class | ISO 1 4H |
| Tolerance class | ISO 1X 4HX |
| Tolerance class | ISO 2 6H |
| Tolerance class | ISO 2X 6HX |
| Tolerance class | 6H +0.05 |
| Tolerance class | ISO 3 6G |
| Tolerance class | ISO 3X 6GX |
| Tolerance class | 7H |
| Tolerance class | 7HX |
| Tolerance class | 7G |
| Tolerance class | 7GX |
| Tolerance class | 6H +0.10 |
| Tolerance class | 6H +0.20 |
| Tool material | HSS E |
| Number of cutting edges Z | 3 |
| Thread type | MF-LH |
| Thread size | M14×1 |
| Coating | uncoated |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | B |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for through holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |

| | |
|-----------------|---------|
| Colour ring | without |
| Type of product | Tap |