

Garant**Left-hand thread through hole machine tap, uncoated, MF: M17X1,75****Order data**

Order number	130001 M17X1,75
GTIN	4062406001353
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 1.75 mm

Overall length L: 125 mm

Shank $\varnothing D_s$: 14 mmShank square \square : 11 mmTapping hole \varnothing : 15.25 mm**Technical description**

Thread depth	51 mm
Shank $\varnothing D_s$	14 mm
Thread pitch	1.75 mm
Thread \varnothing	17 mm
Tool material	HSS E
Tapping hole \varnothing	15.25 mm

Shank square □	11 mm
Number of cutting edges Z	3
Number of clamping slots	3
Standard	DIN 376
Overall length L	125 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Thread type	MF-LH
Thread size	M17×1.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap