

**Garant****Left-hand thread through hole machine tap, TiN, MF: M14X0,35****Order data**

Order number	130006 M14X0,35
GTIN	4062406008208
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.35 mm

Overall length L: 110 mm

Shank  $\varnothing$  D<sub>s</sub>: 11 mmShank square  $\square$ : 9 mmTapping hole  $\varnothing$ : 13.65 mm**Technical description**

Standard	DIN 376
Tool material	HSS E
Number of cutting edges Z	3
Number of clamping slots	3
Tapping hole $\varnothing$	13.65 mm
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Shank $\varnothing D_s$	11 mm
Thread pitch	0.35 mm
Thread depth	42 mm
Overall length L	110 mm
Shank square $\square$	9 mm
Thread $\varnothing$	14 mm
Thread type	MF-LH
Thread size	M14x0.35
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3xD for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap