

**Garant****Left-hand thread through hole machine tap, TiN, MF: M2,2X0,2****Order data**

Order number	130006 M2,2X0,2
GTIN	4062406007539
Item class	10N

**Description****Note:**

Delivery time: 91 calendar days  
Minimum order quantity: 25 pcs.  
Special / custom-made product - return not possible  
Thread type: MF-LH  
Tool material: HSS E  
Standard: DIN 371  
Tolerance class: ISO 1 4H  
Tolerance class: ISO 1X 4HX  
Tolerance class: ISO 2 6H  
Thread pitch: 0.2 mm  
Overall length L: 45 mm  
Shank  $\varnothing D_s$ : 2.8 mm  
Shank square  $\square$ : 2.1 mm  
Tapping hole  $\varnothing$ : 2 mm

**Technical description**

Overall length L	45 mm
Tool material	HSS E
Thread pitch	0.2 mm
Thread depth	6.6 mm
Shank $\varnothing D_s$	2.8 mm
Standard	DIN 371

Shank square □	2.1 mm
Tapping hole Ø	2 mm
Number of cutting edges Z	3
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread Ø	2.2 mm
Number of clamping slots	3
Thread type	MF-LH
Thread size	M2.2×0.2
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap