

**Garant****Through hole machine tap, TiN, MF: M52X3****Order data**

Order number	130005 M52X3
GTIN	4062406007324
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 3 mm

Overall length L: 250 mm

Shank Ø D<sub>s</sub>: 40 mm

Shank square □: 32 mm

Tapping hole Ø: 49 mm

**Technical description**

Standard	DIN 376
Shank Ø D <sub>s</sub>	40 mm
Overall length L	250 mm
Number of cutting edges Z	4
Number of clamping slots	4
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread pitch	3 mm
Thread depth	156 mm
Tool material	HSS E
Shank square <input type="checkbox"/>	32 mm
Tapping hole Ø	49 mm
Thread Ø	52 mm
Thread type	M
Thread size	M52×3
Coating	TiN
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring

without

Type of product

Tap