

**Garant****Left-hand thread through hole machine tap, uncoated, MF: M35X0,5****Order data**

Order number	130001 M35X0,5
GTIN	4062406002725
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 200 mm

Shank  $\varnothing$  D<sub>s</sub>: 28 mmShank square  $\square$ : 22 mmTapping hole  $\varnothing$ : 34.5 mm**Technical description**

Tapping hole $\varnothing$	34.5 mm
Standard	DIN 376
Thread pitch	0.5 mm
Overall length L	200 mm
Thread depth	105 mm
Thread $\varnothing$	35 mm

Shank square □	22 mm
Tool material	HSS E
Number of cutting edges Z	4
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Number of clamping slots	4
Shank $\varnothing D_s$	28 mm
Thread type	MF-LH
Thread size	M35×0.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap