

Garant**Left-hand thread through hole machine tap, TiN, MF: M24X1****Order data**

| | |
|--------------|---------------|
| Order number | 130006 M24X1 |
| GTIN | 4062406009014 |
| Item class | 10N |

Description**Note:**

Delivery time: 49 calendar days
Minimum order quantity: 1 pc.
Special / custom-made product - return not possible
Thread type: MF-LH
Tool material: HSS E
Standard: DIN 376
Tolerance class: ISO 1 4H
Tolerance class: ISO 1X 4HX
Tolerance class: ISO 2 6H
Thread pitch: 1 mm
Overall length L: 160 mm
Shank $\varnothing D_s$: 18 mm
Shank square \square : 14.5 mm
Tapping hole \varnothing : 23 mm

Technical description

| | |
|---------------------------|----------|
| Thread pitch | 1 mm |
| Number of cutting edges Z | 3 |
| Thread depth | 72 mm |
| Thread \varnothing | 24 mm |
| Shank $\varnothing D_s$ | 18 mm |
| Tolerance class | ISO 1 4H |

| | |
|----------------------------------|--|
| Tolerance class | ISO 1X 4HX |
| Tolerance class | ISO 2 6H |
| Tolerance class | ISO 2X 6HX |
| Tolerance class | 6H +0.05 |
| Tolerance class | 6H +0.20 |
| Tolerance class | ISO 3 6G |
| Tolerance class | ISO 3X 6GX |
| Tolerance class | 7H |
| Tolerance class | 7HX |
| Tolerance class | 7G |
| Tolerance class | 7GX |
| Tolerance class | 6H +0.10 |
| Tool material | HSS E |
| Tapping hole Ø | 23 mm |
| Standard | DIN 376 |
| Shank square □ | 14.5 mm |
| Overall length L | 160 mm |
| Number of clamping slots | 3 |
| Thread type | MF-LH |
| Thread size | M24×1 |
| Coating | TiN |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | B |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for through holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |

| | |
|-----------------|---------|
| Colour ring | without |
| Type of product | Tap |