

Garant
Left-hand thread through hole machine tap, uncoated, MF: M43X0,75

Order data

Order number	130001 M43X0,75
GTIN	4062406003319
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.75 mm

Overall length L: 220 mm

Shank $\varnothing D_s$: 36 mm

Shank square \square : 29 mm

Tapping hole \varnothing : 42.25 mm

Technical description

Number of cutting edges Z	4
Shank $\varnothing D_s$	36 mm
Thread depth	129 mm
Standard	DIN 376
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX

Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Number of clamping slots	4
Shank square □	29 mm
Tool material	HSS E
Overall length L	220 mm
Thread pitch	0.75 mm
Tapping hole Ø	42.25 mm
Thread Ø	43 mm
Thread type	MF-LH
Thread size	M43×0.75
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap