

**Garant**
**Left-hand thread through hole machine tap, TiN, MF: M28X0,75**

**Order data**

Order number	130006 M28X0,75
GTIN	4062406009342
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: MF-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Tolerance class: ISO 1 4H  
 Tolerance class: ISO 1X 4HX  
 Tolerance class: ISO 2 6H  
 Thread pitch: 0.75 mm  
 Overall length L: 140 mm  
 Shank  $\varnothing D_s$ : 20 mm  
 Shank square  $\square$ : 16 mm  
 Tapping hole  $\varnothing$ : 27.25 mm

**Technical description**

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20

Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Overall length L	140 mm
Thread depth	84 mm
Standard	DIN 376
Number of cutting edges Z	4
Thread pitch	0.75 mm
Tool material	HSS E
Tapping hole $\varnothing$	27.25 mm
Shank square $\square$	16 mm
Shank $\varnothing D_s$	20 mm
Thread $\varnothing$	28 mm
Number of clamping slots	4
Thread type	MF-LH
Thread size	M28x0.75
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3xD for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap