

Garant
Left-hand thread through hole machine tap, TiN, MF: M4X0,7

Order data

Order number	130006 M4X0,7
GTIN	4062406007683
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: M-LH

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.7 mm

Overall length L: 63 mm

Shank $\varnothing D_s$: 4.5 mm

Shank square \square : 3.4 mm

Tapping hole \varnothing : 3.3 mm

Technical description

Number of cutting edges Z	3
Tapping hole \varnothing	3.3 mm
Tool material	HSS E
Shank square \square	3.4 mm
Overall length L	63 mm
Shank $\varnothing D_s$	4.5 mm

Number of clamping slots	3
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread depth	12 mm
Standard	DIN 371
Thread pitch	0.7 mm
Thread Ø	4 mm
Thread type	M-LH
Thread size	M4×0.7
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap