

**Garant**
**Left-hand thread through hole machine tap, uncoated, MF: M9X1,25**

**Order data**

Order number	130001 M9X1,25
GTIN	4062406000790
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 3 pcs.  
 Special / custom-made product - return not possible  
 Thread type: M-LH  
 Tool material: HSS E  
 Standard: DIN 371  
 Tolerance class: ISO 1 4H  
 Tolerance class: ISO 1X 4HX  
 Tolerance class: ISO 2 6H  
 Thread pitch: 1.25 mm  
 Overall length L: 90 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 9 mm  
 Shank square  $\square$ : 7 mm  
 Tapping hole  $\varnothing$ : 7.75 mm

**Technical description**

Thread $\varnothing$	9 mm
Tool material	HSS E
Thread pitch	1.25 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H

Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Shank square □	7 mm
Thread depth	27 mm
Shank Ø D <sub>s</sub>	9 mm
Tapping hole Ø	7.75 mm
Number of cutting edges Z	3
Overall length L	90 mm
Standard	DIN 371
Number of clamping slots	3
Thread type	M-LH
Thread size	M9×1.25
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap