

Garant
Left-hand thread through hole machine tap, uncoated, MF: M3,5X0,35

Order data

| | |
|--------------|------------------|
| Order number | 130001 M3,5X0,35 |
| GTIN | 4062406000493 |
| Item class | 10N |

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 3 pcs.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS E
 Standard: DIN 371
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 0.35 mm
 Overall length L: 56 mm
 Shank $\varnothing D_s$: 4 mm
 Shank square \square : 3 mm
 Tapping hole \varnothing : 3.15 mm

Technical description

| | |
|---------------------------|------------|
| Number of cutting edges Z | 3 |
| Tool material | HSS E |
| Tolerance class | ISO 1 4H |
| Tolerance class | ISO 1X 4HX |
| Tolerance class | ISO 2 6H |
| Tolerance class | ISO 2X 6HX |

| | |
|----------------------------------|--|
| Tolerance class | 6H +0.05 |
| Tolerance class | ISO 3 6G |
| Tolerance class | ISO 3X 6GX |
| Tolerance class | 7H |
| Tolerance class | 7HX |
| Tolerance class | 7G |
| Tolerance class | 7GX |
| Tolerance class | 6H +0.10 |
| Tolerance class | 6H +0.20 |
| Tapping hole Ø | 3.15 mm |
| Shank Ø D _s | 4 mm |
| Shank square □ | 3 mm |
| Number of clamping slots | 3 |
| Thread Ø | 3.5 mm |
| Thread pitch | 0.35 mm |
| Thread depth | 10.5 mm |
| Standard | DIN 371 |
| Overall length L | 56 mm |
| Thread type | MF-LH |
| Thread size | M3.5×0.35 |
| Coating | uncoated |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | B |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for through holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |

| | |
|-----------------|---------|
| Colour ring | without |
| Type of product | Tap |