

Garant**Left-hand thread through hole machine tap, TiN, MF: M3X0,5****Order data**

Order number	130006 M3X0,5
GTIN	4062406007621
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: M-LH

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 56 mm

Shank $\varnothing D_s$: 3.5 mmShank square \square : 2.7 mmTapping hole \varnothing : 2.5 mm**Technical description**

Overall length L	56 mm
Thread pitch	0.5 mm
Shank $\varnothing D_s$	3.5 mm
Tapping hole \varnothing	2.5 mm
Number of clamping slots	3
Standard	DIN 371

Tool material	HSS E
Thread depth	9 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Number of cutting edges Z	3
Thread Ø	3 mm
Shank square □	2.7 mm
Thread type	M-LH
Thread size	M3×0.5
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap