

Garant
Left-hand thread through hole machine tap, uncoated, MF: M52X2

Order data

Order number	130001 M52X2
GTIN	4062406003746
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS E
 Standard: DIN 376
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 2 mm
 Overall length L: 250 mm
 Shank \varnothing D_s: 40 mm
 Shank square \square : 32 mm
 Tapping hole \varnothing : 50 mm

Technical description

Thread \varnothing	52 mm
Shank square \square	32 mm
Thread depth	156 mm
Standard	DIN 376
Number of clamping slots	4
Tool material	HSS E

Number of cutting edges Z	4
Overall length L	250 mm
Thread pitch	2 mm
Tapping hole Ø	50 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Shank Ø D _s	40 mm
Thread type	MF-LH
Thread size	M52×2
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap