

Garant**Left-hand thread through hole machine tap, uncoated, MF: M50X4****Order data**

Order number	130001 M50X4
GTIN	4062406003678
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 4 mm

Overall length L: 250 mm

Shank \varnothing D_s: 40 mmShank square \square : 32 mmTapping hole \varnothing : 46 mm**Technical description**

Tool material	HSS E
Thread depth	150 mm
Number of clamping slots	4
Overall length L	250 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX

Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Shank square □	32 mm
Number of cutting edges Z	4
Standard	DIN 376
Thread Ø	50 mm
Tapping hole Ø	46 mm
Shank Ø D _s	40 mm
Thread pitch	4 mm
Thread type	MF-LH
Thread size	M50×4
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap