

**Garant**
**Spiral flute machine tap, uncoated, MF: M45X3**

**Order data**

Order number	130010 M45X3
GTIN	4062406014155
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 3 mm

Overall length L: 220 mm

Shank  $\varnothing D_s$ : 36 mm

Shank square  $\square$ : 29 mm

Tapping hole  $\varnothing$ : 42 mm

**Technical description**

Number of clamping slots	4
Standard	DIN 376
Thread depth	112.5 mm
Shank $\varnothing D_s$	36 mm
Overall length L	220 mm
Thread $\varnothing$	45 mm

Shank square □	29 mm
Number of cutting edges Z	4
Thread pitch	3 mm
Tool material	HSS E
Tapping hole Ø	42 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Thread type	M
Thread size	M45×3
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap