

**Garant**
**Spiral flute machine tap, uncoated, MF: M4X0,5**

**Order data**

Order number	130010 M4X0,5
GTIN	4062406011246
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

**Technical description**

Shank square <input type="checkbox"/>	3.4 mm
Number of clamping slots	3
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G

Tolerance class	7GX
Tolerance class	6H +0.10
Thread depth	10 mm
Number of cutting edges Z	3
Tool material	HSS E
Shank $\varnothing D_s$	4.5 mm
Thread pitch	0.5 mm
Thread $\varnothing$	4 mm
Tapping hole $\varnothing$	3.5 mm
Overall length L	63 mm
Standard	DIN 371
Thread type	M
Thread size	M4x0.5
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap