

**Garant**
**Spiral flute machine tap, uncoated, MF: M10X0,75**

**Order data**

Order number	130010 M10X0,75
GTIN	4062406011543
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

**Technical description**

Standard	DIN 371
Thread pitch	0.75 mm
Shank square $\square$	8 mm
Tapping hole $\varnothing$	9.25 mm
Overall length L	100 mm
Thread $\varnothing$	10 mm
Number of cutting edges Z	3
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20

Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Number of clamping slots	3
Shank $\varnothing D_s$	10 mm
Thread depth	25 mm
Tool material	HSS E
Thread type	M
Thread size	M10x0.75
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap