

Garant**Left-hand thread through hole machine tap, TiN, MF: M46X0,75****Order data**

Order number	130006 M46X0,75
GTIN	4062406010591
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.75 mm

Overall length L: 250 mm

Shank \varnothing D_s: 36 mm

Shank square □: 29 mm

Tapping hole \varnothing : 45.25 mm**Technical description**

Standard	DIN 376
Thread depth	138 mm
Number of cutting edges Z	4
Overall length L	250 mm
Thread \varnothing	46 mm
Thread pitch	0.75 mm

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tapping hole Ø	45.25 mm
Tool material	HSS E
Shank Ø D _s	36 mm
Shank square □	29 mm
Number of clamping slots	4
Thread type	MF-LH
Thread size	M46×0.75
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap