

Garant
Spiral flute machine tap, uncoated, MF: M10X1,25

Order data

Order number	130010 M10X1,25
GTIN	4062406011567
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Technical description

Thread pitch	1.25 mm
Tool material	HSS E
Overall length L	100 mm
Standard	DIN 371
Number of clamping slots	3
Shank square <input type="checkbox"/>	8 mm
Thread \varnothing	10 mm
Thread depth	25 mm
Number of cutting edges Z	3
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX

Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tapping hole Ø	8.75 mm
Shank Ø D _s	10 mm
Thread type	M
Thread size	M10×1.25
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap