

**Garant**
**Through hole machine tap, TiN, MF: M36X1**

**Order data**

Order number	130005 M36X1
GTIN	4062406006396
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 1 mm

Overall length L: 200 mm

Shank  $\varnothing D_s$ : 28 mm

Shank square  $\square$ : 22 mm

Tapping hole  $\varnothing$ : 35 mm

**Technical description**

Shank $\varnothing D_s$	28 mm
Tool material	HSS E
Tapping hole $\varnothing$	35 mm
Number of clamping slots	4
Standard	DIN 376
Tolerance class	ISO 1 4H

Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Overall length L	200 mm
Thread depth	108 mm
Shank square □	22 mm
Number of cutting edges Z	4
Thread Ø	36 mm
Thread pitch	1 mm
Thread type	M
Thread size	M36×1
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap