

**Garant**
**Through hole machine tap, TiN, MF: M2X0,2**

**Order data**

Order number	130005 M2X0,2
GTIN	4062406003920
Item class	10N

**Description**
**Note:**

Delivery time: 91 calendar days

Minimum order quantity: 25 pcs.

Special / custom-made product - return not possible

**Technical description**

Number of cutting edges Z	3
Tapping hole Ø	1.8 mm
Shank Ø D <sub>s</sub>	2.8 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G

Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Tool material	HSS E
Overall length L	45 mm
Shank square □	2.1 mm
Standard	DIN 376
Thread Ø	2 mm
Thread depth	6 mm
Thread pitch	0.2 mm
Number of clamping slots	3
Thread type	M
Thread size	M2×0.2
Coating	TiN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap