

Garant
Left-hand thread through hole machine tap, TiN, MF: M1,2X0,2

Order data

Order number	130006 M1,2X0,2
GTIN	4062406007386
Item class	10N

Description
Note:

Delivery time: 91 calendar days
 Minimum order quantity: 25 pcs.
 Special / custom-made product - return not possible
 Thread type: MF-LH
 Tool material: HSS E
 Standard: DIN 371
 Tolerance class: ISO 1 4H
 Tolerance class: ISO 1X 4HX
 Tolerance class: ISO 2 6H
 Thread pitch: 0.2 mm
 Overall length L: 40 mm
 Shank $\varnothing D_s$: 2.5 mm
 Shank square \square : 2.1 mm
 Tapping hole \varnothing : 1 mm

Technical description

Shank square \square	2.1 mm
Overall length L	40 mm
Tool material	HSS E
Thread pitch	0.2 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX

Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Number of cutting edges Z	2
Standard	DIN 371
Tapping hole \varnothing	1 mm
Shank $\varnothing D_s$	2.5 mm
Number of clamping slots	2
Thread depth	3.6 mm
Thread \varnothing	1.2 mm
Thread type	MF-LH
Thread size	M1.2×0.2
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap