

**Garant****Left-hand thread through hole machine tap, TiN, MF: M18X0,5****Order data**

Order number	130006 M18X0,5
GTIN	4062406008529
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days  
Minimum order quantity: 2 pcs.  
Special / custom-made product - return not possible  
Thread type: MF-LH  
Tool material: HSS E  
Standard: DIN 376  
Tolerance class: ISO 1 4H  
Tolerance class: ISO 1X 4HX  
Tolerance class: ISO 2 6H  
Thread pitch: 0.5 mm  
Overall length L: 125 mm  
Shank  $\varnothing$  D<sub>s</sub>: 14 mm  
Shank square  $\square$ : 11 mm  
Tapping hole  $\varnothing$ : 17.5 mm

**Technical description**

Number of cutting edges Z	3
Thread pitch	0.5 mm
Thread depth	54 mm
Shank square $\square$	11 mm
Standard	DIN 376
Number of clamping slots	3

Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tapping hole Ø	17.5 mm
Tool material	HSS E
Overall length L	125 mm
Shank Ø D <sub>s</sub>	14 mm
Thread Ø	18 mm
Thread type	MF-LH
Thread size	M18×0.5
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap