

Garant**Left-hand thread through hole machine tap, TiN, MF: M20X0,75****Order data**

Order number	130006 M20X0,75
GTIN	4062406008703
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: MF-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 0.75 mm

Overall length L: 140 mm

Shank $\varnothing D_s$: 16 mmShank square \square : 12 mmTapping hole \varnothing : 19.25 mm**Technical description**

Tool material	HSS E
Number of cutting edges Z	3
Shank square \square	12 mm
Thread depth	60 mm
Shank $\varnothing D_s$	16 mm
Thread \varnothing	20 mm

Thread pitch	0.75 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Standard	DIN 376
Number of clamping slots	3
Tapping hole Ø	19.25 mm
Overall length L	140 mm
Thread type	MF-LH
Thread size	M20×0.75
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap