

Garant**Left-hand thread blind hole machine tap, uncoated, MF: M12X1****Order data**

Order number	130011 M12X1
GTIN	4062406015275
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: MF-LH
Tool material: HSS E
Standard: DIN 376
Tolerance class: ISO 1 4H
Tolerance class: ISO 1X 4HX
Tolerance class: ISO 2 6H
Thread pitch: 1 mm
Overall length L: 110 mm
Shank \varnothing D_s: 9 mm
Shank square \square : 7 mm
Tapping hole \varnothing : 11 mm

Technical description

Thread \varnothing	12 mm
Standard	DIN 376
Tool material	HSS E
Thread pitch	1 mm
Shank square \square	7 mm
Number of cutting edges Z	2

Thread depth	30 mm
Overall length L	110 mm
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	6H +0.20
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tapping hole Ø	11 mm
Number of clamping slots	2
Shank Ø D _s	9 mm
Thread type	MF-LH
Thread size	M12×1
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap